

## SL-F15B Stratlock™ Female Front Mount

INDUSTRY FIT:



### SPECIFICATIONS:

### STRATLOCK SL RANGE

The SL-F15B provides rapid installation of heavy panels into 18mm standard galvanized steel rail framework. Designed specifically for contract interior fit out applications. Female installs rapidly with a push fit function into the steel channel, and does not require fastenings. Used with the SL-M15, the set provides 360° panel adjustment before locking into place with a 15kg pull out load. Patent Pending.

Fits into channel dimensions: mouth: 35.0mm - 35.75mm, depth: min 15.75mm - 16.5mm, wall thickness: N/A.

**SL-F15B** 15kg



**USE WITH:**  
SL-M15



### NEW PRODUCT

#### MATERIAL:

White acetyl, rubber o-ring

#### MORE INFO:

Installation Guide SL-F15B  
Clip Layout Guide TD-16



### BENEFITS

- Strongest mounting available from Fastmount
- 360° panel adjustment of panel before locking into place
- Push fit into rail face
- No special tools required
- Acoustic isolation between panel and frame
- Fits into front channel steel extrusion
- 15kg pull out load
- Adjustability along channel for easy spacing - no drilling required

### APPLICATIONS

- Commercial interior fit out
- Mounting heavier ceiling and wall panels
- Architectural applications
- Hotels, hospitals, retail, residential

### INSTALLATION: Partially exploded through section showing typical installation method



- A Channel Depth: Min 15.75mm - 16.5mm  
B Channel Mouth: 35.0mm - 35.75mm  
C (Channel Wall Thickness: Wall thickness does not effect clip)


The Fastmount® multi-award winning system has revolutionized the mounting of panels. Panels can easily be removed and refitted in any sequence time after time. For further information or technical support contact: [info@fastmount.com](mailto:info@fastmount.com)

[www.fastmount.com](http://www.fastmount.com)



## SL-F15B Stratlock™ Range Screw Fix

### SL-F15B



#### USE WITH:

SL-M15



#### INSTALL WITH:

#8 screw

### INSTALLATION STEPS Screw fix method

<p><b>1</b> Push fit SL-F15B into frame</p>	<p><b>2</b> Locate SL-F15B into correct position</p>	<p><b>3</b> Insert CP-01 ST into SL-F15B and press panel into correct position, marking the panel</p>	<p><b>4</b> Drill out mark created by CP-01ST with 3mm drill bit</p>
<p><b>5</b> Install SL-M15 with #8 screw</p>	<p><b>6</b> Engage panel to first click into SL-F15B</p>	<p><b>7</b> Adjust panel 360° to find correct position</p>	<p><b>8</b> Once panel is in correct location, engage second click by pressing panel into final position</p>

## SL-F15B Stratlock™ Range Adhesive Fix

### SL-F15B



#### USE WITH:

SL-M15



#### INSTALL WITH:

Fastmount SuperGroove®  
Adhesive

### INSTALLATION STEPS Adhesive fix method

<p><b>1</b> Push fit SL-F15B into frame</p>	<p><b>2</b> Locate SL-F15B into correct position</p>	<p><b>3</b> Engage SL-M15 two clicks into SL-F15B</p>	<p><b>4</b> Apply Fastmount SuperGroove Adhesive CG-5010 to SL-M15</p>
<p><b>5</b> Press panel into place</p>	<p><b>6</b> Use panel support while adhesive dries</p>	<p><b>7</b> Once adhesive has dried, remove panel. Replace and engage only one click to adjust panel around the SL-M15's point</p>	<p><b>8</b> Once panel is in desired location, engage second click by pressing panel into its final position</p>